INFO SHEET

Spacesaver's RS24 Large Evidence Refrigerator

Designed and developed by Spacesaver for the needs of unattended refrigerated evidence drop off, the RS24 Large Evidence Refrigerator raises the benchmark in refrigerated evidence handling for today and into the future; Available for both the "Pass Thru" and "Non-Pass Thru" processes.

STANDARD FEATURES

- Modular construction, units shipped fully assembled and ready to use.
- Standard configurations measuring same as evidence lockers (82"H x 36"W x 24"D)
- Stainless steel interior and exterior
- Stainless steel handle on front and rear door
- Maintains preset controlled temperature of 38°F to 42°F (3°C to 5.5°C)
- "Power ON" digital temperature display
- Audible alarm preset at 36°F (Low) and 44°F (High)
- Keyless locking system prevents re-access by depositor to secure evidence
- Available in Pass-Thru and Non Pass-Thru models
- Nine (9) standard interior configurations allow 4 to 24 compartments
- Condensation free door jams
- Magnetic seal on main doors
- Defrost cycle (twice per day)
- 404A Refrigerant
- Separate cold pack compartment and lockable door for easy access and maintenance
- Powered by 115V / 20 amp dedicated
- CUL and UL certified
- Number tags installed on all front doors
- Adjustable floor levelers in base
- Sturdy main door hinges for longevity
- Wall trim packages included on Pass-thru models
- All installation hardware included




- Lifetime warranty on the structural frame
- One (1) year limited warranty on refrigeration units
- Two (2) year limited warranty on electrical components and wiring


OPTIONS

Available compartments:
4, 6, 8, 9, 10, 12, 15, 18 or 24




BASIC DIMENSIONS





STANDARD INTERIOR DOOR CONFIGURATIONS



••	• 0
• •	• 0
	1-6

• 0			- ◊
- 0			• •
• •	Page • O		- ◊
-0-0			• ◊
RS2	4-8	ı Li	RS2

		MODEL # AND # OF OPENINGS	OPENING HEIGHT	H.S. WIDTH *	NON H.S. WIDTH **	
		RS24-4	22 3/8"	11 3/4"	12 3/8	
- <u>ii</u> c • ◊	⊕ • ٥	RS24-6	14 7/8"	11 3/4"	12 3/8	
		RS24-8	11 1/8"	11 3/4"	12 3/8	
• • • • • • • • • • • • • • • • • • • •	RS24-10	8 7/8"	11 3/4"	12 3/8		
	-	RS24-12	7 3/8"	11 3/4"	12 3/8	
	RS24-9	14 7/8"	6 7/8"	7 5/8		
		RS24-15	8 7/8"	6 7/8"	7 5/8	
• •	•••	RS24-18	7 3/8"	6 7/8"	7 5/8	
DC24	10	RS24-24	5 1/2"	6 7/8"	7 5/8	
RS24	-10					

H.S. IDTH *	NON H.S. WIDTH **	Depth: All compartments 17 1/4"
1 3/4"	12 3/8	
1 3/4"	12 3/8	* H.S. Width Vertical compartments on hinge side of locker when front
1 3/4"	12 3/8	main door is open 180°.
1 3/4"	12 3/8	Deduct 1" for 90° opening.
1 3/4"	12 3/8	** Non H.S. Width Width of all other
7/8"	7 5/8	compartments.
7/8"	7 5/8	Add PT for Pass-thru
7/8"	7 5/8	Add F F for Pass-tiffu
7/8"	7 5/8	

	• 0
- 0	• •
- o	• •
-0	• 0
-0	• 0

■ • •	• 0	••
iši • ◊	•••	
	••	[10] [10] [10] [10] [10] [10] [10] [10]

⊕ • ◊	oğri ● O	- o
• 0		- 0
		[2]55 ● ◊
. 0	1	• 0

- 0 - 0	• •	. • •
- 0	::::• o	:::• ◊
	::::• o	· • •
- O	- ¢	
eğs • ¢	. 0	-6-0

.0	. 0	1960 • 1
. 0	• 0	·
. 0	• 0	- c
. 0	• 0	1961 • C
. 0	• 0	
· 0	• 0	10 min (
ĕ • 0	. 0	- C
. 0		0 (m)

All dimensions shown indicate maximum size of evidence container that can be put into compartment. Custom configurations available on request.



Spacesaver Corporation 1450 Janesville Avenue Fort Atkinson, WI 53538-2798 800.492.3434 www.spacesaver.com